

porteril

DOUBLE 320



| TECHNICAL INFORMATION | |
|---------------------------|---|
| Dimensions | 2.10 x 1.60 x 0.82 m |
| Shell | Coril [®] White or Sterling Silver |
| Panels | Alupanels |
| Weight without water | 300 Kg |
| Weight with water | 1.250 Кg |
| Volume | 2.8 m ³ |
| EQUIPMENT SPECIFICATIONS | |
| Seats | 3 (2 lounged) |
| Filter | 1 (3.25 m ²) |
| Water Capacity | 950 l |
| Drain Valve | 1 |
| TECHNICAL SPECIFICATIONS | DELUXE |
| Jets | 55 |
| Circulation Pump | 1-60 W |
| Massage Pump | 2 – 2200 W |
| Blower | 1 – 850 W |
| Disinfection system | UV & Ozone |
| Control box with heater | 1 – 3000 W |
| Illumination | Multipoint |
| ELECTRICAL SPECIFICATIONS | |
| Voltage | 220-240 V ~ or 380-415 V ~ |
| Max Absorbed Power | 5310 W |
| Frequency | 50 Hz |
| Amperage | 25A or 3x16A |

Note : the standard measures may vary ±2cm



IMPORTANT: Important: The equipment must be connected to an exclusive and permanent power line capable to support installed power. Lighting and electrical receptacles must be located at least 1.5 meters from the equipment.

The circuit ground wire must be provided to take advantage of the designed-in safety features of the equipment.

The electric installation must be in accordance with actual legislation.